

Glycerine-filled pressure gauges, connection radial on bottom



Tips

213.40

Modelis

Caurules atspermanometrs ar glicerīna pildījumu

Izmantošana

For gaseous or liquid media which do not corrode copper alloy, do not have high viscosity and do not crystallise

Kvalitātes klase

1,0

Vides temperatūra

no -20 °C līdz +60 °C

Vielas temperatūra

maks. +60 °C

Gredzenveida apmale

CrNi steel

Korpuss

Pressed brass

Mērelements

Copper alloy (Ø 63), Copper alloy < 100 bar>; CrNi steel 1.4571 ≥ 100 bar (Ø 100)

Rādītāja mehānisms

Copper alloy

Skatstikls

Plexiglass

Apraksts

Mērišanas vietām ar augstu, dinamisku spiediena noslodzi un vibrācijām

Norādīt

Citi dati pieejami pēc pieprasījuma.

Produkts

Apzīmējums	Mērišanas diapazons	Ø mm	Savienojums
K- 07 20 02 32	-1 / 0.0 bar	100.0	G 1/2"
K- 07 20 02 33	-1 / +0.6 bar	100.0	G 1/2"
K- 07 20 02 34	-1 / +1.5 bar	100.0	G 1/2"
K- 07 20 02 35	-1 / +3.0 bar	100.0	G 1/2"
K- 07 20 02 36	-1 / +5.0 bar	100.0	G 1/2"
K- 07 20 02 37	-1 / +9.0 bar	100.0	G 1/2"
K- 07 20 02 38	-1 / +15.0 bar	100.0	G 1/2"
K- 07 20 02 39	0 - 0.6 bar	100.0	G 1/2"
K- 07 20 02 40	0 - 1.0 bar	100.0	G 1/2"
K- 07 20 02 41	0 - 1.6 bar	100.0	G 1/2"
K- 07 20 02 42	0 - 2.5 bar	100.0	G 1/2"
K- 07 20 02 43	0 - 4.0 bar	100.0	G 1/2"
K- 07 20 02 44	0 - 6.0 bar	100.0	G 1/2"
K- 07 20 02 45	0 - 10.0 bar	100.0	G 1/2"
K- 07 20 02 46	0 - 16.0 bar	100.0	G 1/2"
K- 07 20 02 47	0 - 25.0 bar	100.0	G 1/2"
K- 07 20 02 48	0 - 40.0 bar	100.0	G 1/2"
K- 07 20 02 49	0 - 60.0 bar	100.0	G 1/2"
K- 07 20 02 50	0 - 100.0 bar	100.0	G 1/2"
K- 07 20 02 51	0 - 160.0 bar	100.0	G 1/2"
K- 07 20 02 52	0 - 250.0 bar	100.0	G 1/2"
K- 07 20 02 53	0 - 400.0 bar	100.0	G 1/2"
K- 07 20 02 54	0 - 600.0 bar	100.0	G 1/2"
K- 07 20 02 55	0 - 1000.0 bar	100.0	G 1/2"